## Catches Push Catches





Rail plate mounting (Short version)

Rail plate mounting

41.5

Push

to open

85

Short version

**Close** position

\_\_\_\_\_1.8 min

Open position

14 min

Adjustment to

align doors

- 19 j-

(Long version)

42.5

1<sup>9</sup>

9.5 -

K Push (Short version)

14.5

K Push (Long version)

14.5

ī

Ŧ

## **B** K Push and plate - short or long version

 Available either with magnet or with buffer With magnet for cabinets using unsprung or negative hinges

With buffer for cabinets using sprung hinges

- Screw fixing rail plate with wood screws 3 x 16 mm (not provided)
- K Push slides onto rail plate and clicks in
- Important: please do not press or release the spring until the K Push is fully installed
  Engineering plattic with magnet or where
- Engineering plastic with magnet or rubber buffer
- Order K Push and rail plate separately
- Black and white versions available, contact us for more information

K Push in grey - short version	
Item	Cat. No.
Push catch, with buffer	356.01.501
Push catch, with magnet	356.01.511
Rail plate	356.01.519
Adhesive plate for magnet	356.01.539
Plate for magnet, with Ø 3 mm pin	
	356.01.549

## Order qty: 1 pc

K Push in grey - long version	
Item	Cat. No.
Push catch, with buffer	356.01.502
Push catch, with magnet	356.01.512
Rail plate	356.01.519
Adhesive plate for magnet	356.01.539
Plate for magnet, with Ø 3 mm pin	
	356.01.549

Order qty: 1 pc







K Push short with buffer



